



YORK® Air Curtain

Hawk Series

Features & Benefits

Ceiling Type Hawk Series

Application: High-grade glass door which cannot install horizontally, or the vertical side without enough space and other special environments.

Easy Clean and Fireproof

Full Steel Cabinet and Stainless steel air inlet covers, rust-proof and easy clean

Easy Operation

Selectable high and lower air velocity controlled by remote control or key switch

Recessed in Ceiling Design

Recessed in ceiling or hang on ceiling type design, it's for special situations where the glass door is unable or lacks of enough space for side installation. Apply high velocity motor, centrifugal turbine fan and scientific air duct design; powerful air pressure and lower noise operation

Features:

- Stainless steel grille / White powder coated grille
- Centrifugal flow, 2-speed fans
- Adjustable air deflector
- Luxury design
- Remote control (optional)
- Magnetic door switch (optional)



Metal Casing



High Efficient Motor



Quiet Centrifugal Flow Fan



Adjustable Air Deflector



Remote Control



Touch Control



Application: For offices, high grade restaurants and department stores and more

Finish available: Stainless steel grille / White powder coated steel

Technical Specifications

Model No.	Dimensions (mm)	Voltage (V~)	Frequency (Hz)	Air Velocity High/Low (m/s)	Air Volume High/Low (m³/h)	Noise Level High/Low (dB)	Power High/Low (W)	Net Weight (kg)
YAC3509CSL	900X235X320	220-240	50 / 60	16/13	1100 / 900	52 / 49	230 / 200	17.0
YAC3510CSL	1000X235X320	220-240	50 / 60	16/13	1200 / 1000	52 / 49	250 / 220	19.0
YAC3512CSL	1200X235X320	220-240	50 / 60	16/13	1500 / 1200	53 / 50	290 / 260	22.0
YAC3515CSL	1500X235X320	220-240	50 / 60	16/13	1900 / 1500	55 / 52	380 / 350	27.0
YAC3518CSL	1800X235X320	220-240	50 / 60	16/13	2280 / 1800	57 / 55	450 / 420	30.0
YAC3520CSL	2000X235X320	220-240	50 / 60	16/13	2520 / 2100	58 / 56	470 / 440	32.0
YAC4009CSL	900X235X320	220-240	50 / 60	20 / 16	1400 / 1000	57 / 54	300 / 270	17.0
YAC4010CSL	1000X235X320	220-240	50 / 60	20 / 16	1550 / 1100	57 / 54	320 / 290	19.0
YAC4012CSL	1200X235X320	220-240	50 / 60	20 / 16	1900 / 1500	58 / 55	400 / 370	22.0
YAC4015CSL	1500X235X320	220-240	50 / 60	20 / 16	2300 / 1900	61 / 58	500 / 470	27.0
YAC4018CSL	1800X235X320	220-240	50 / 60	20 / 16	2850 / 2250	63 / 61	600 / 570	30.0
YAC4020CSL	2000X235X320	220-240	50 / 60	20 / 16	3255 / 2855	64 / 62	620 / 590	32.0

Installation Height: YAC35 Series 3.5 - YAC40 Series 4m

For more information about YORK® Hawk Series please contact your local Johnson Controls representative.

 **YORK®**
INSTALL CONFIDENCE

We reserve the right to change in part or in whole the specifications without prior notice.

Johnson Controls Middle East & Africa (MEA) Headquarters
P.O. Box 31065, 13th Floor, API World Tower, Sheikh Zayed Road, Dubai, United Arab Emirates
Tel +971 4 309 9999 Fax +971 4 309 9792 middleeast.johnsoncontrols.com

© 2019 Johnson Controls


Johnson Controls